



Introduction

The PET-7H24M is a high speed data acquisition devices with a built-in Ethernet communication port for data transfer over a network, and includes 4 high-speed 24-bit differential Analog input channels (128 kHz sample and hold for all 4 channels), 2 Analog Output channels, 3 Digital Input channels, 4 Digital Output channels and 1 Encoder Input channel. The module provides a programmable input range on all analog channels, and the Digital Output can be set to output with short-circuit and over load protection. 1 Encoder Input channel can be configured as Quadrant, Pulse/Direction or CW/CCW input mode. The PET-7H24M also provides 4 kV ESD protection as well as 2500 VDC intra-module isolation.

Trigger Acquisition	Software AD	Analog Threshold
Continuous Mode	20 ~ 60 kHz	-
N Sample Mode	60 ~ 128 kHz	20 ~ 128 kHz

System Specifications

Software		
OS	Windows 7/8/10 and Linux	
Utility	Configuration, graphically display and data logging	
SDK	Windows • Microsoft VC, C#, VB.NET SDK API and Demo • Python Demo • NI LabVIEW Toolkit and Demo Linux • C/C++ library and Demo • .NET library and Demo • Python Demo	
Communication		
Ethernet Port	1 x RJ-45, 10/100 Base-TX	
PoE	Yes, IEEE 802.3af, class 2	
Security	ID, Password and IP Filter	
Protocol	TCP Steaming (Access data by SDK library) Modbus TCP	
LED Indicators		
Status	1 x System, 1 x Ethernet, 1 x PoE	


EMS Protection				
ESD (IEC 61000-4-2)	4 kV Contact for each terminal and 8 kV Air for random Point			
ESD (IEC 61000-4-4)	+/- 4 kV for power			
2-way Isolation				
I/O	2500 VDC			
Power				
Reverse Polarity Protection	Yes			
Powered from Terminal Block	+12 ~ +48 VDC			
Consumption	2.6 W			
Mechanical				
Dimensions (W x L x H)	76 mm x 120 mm x 38 mm			
Installation	DIN-Rail/Wall Mounting			
Casing	Metal			
Environmental				
Operating Temperature	-25 °C ~ +75 °C			
Storage Temperature	-30 °C ~ +80 °C			
Humidity	10 ~ 90 % RH, Non-condensing			

I/O Specifications

Digital Input		
Channels	3	
Contact	Wet Contact	
Sink/Source (NPN/PNP)	Sink/Source	
On Voltage Level	+5 ~ +30 VDC	
Off Voltage Level	2 VDC Max.	
Input Impedance	10 K Ohm	
Isolation	2500 VDC	
Digital Output		
Channels	4	
Туре	Isolated Open Collector	
Sink/Source (NPN/PNP)	Sink	
Load Voltage	+5 ~ +30 VDC	
Load Current	100 mA at 25°C	
Short-circuit Protection	Yes	
Overload Protection	1.3 A	
Isolation	2500 VDC	

Pin Assignments






Analog Input			
Channels	4 differential Simultaneously		
Resolution	24-bit		
Sampling Rate	128 kS/s (Each Channel)		
Bipolar Input (Programmable)	±10 V, ±5 V, ±2.5 V, ±1.25 V, ±0.625 V, ±300 mV, ±150 mV, ±75 mV, ±40 mV, ±20 mV		
FIFO Size	4 k Samples		
Accuracy	±0.01 % of FSR @ ±10 V; ±0.02 % of FSR @ ±5 V, ±2.5 V; ±0.02 % of FSR @ ±1.25V, ±0.625 V; ±0.1 % of FSR @ ±300 mV, ±150 mV; ±0.1 % of FSR @ ±75 mV, ±40 mV; ±0.2 % of FSR @ ±20 mV		
AD Trigger Mode (Programmable)	Software/Analog Threshold Trigger		
Input Impedance	2 M Ohm		
Analog Output			
Channels	2		
Туре	±10 V, ±5 V, 0 ~ 5 V, 0 ~ 10 V		
Resoluction	12-bit		
Accuracy	± 0.01 % of FSR @ ± 10 V, ± 5 V, 0 ~ 10 V; ± 0.02 % of FSR @ 0 ~ 5 V		
Output Capacity	10 V @ 20 mA		
Slew Rate	0.83 V/us		
Encoder Input			
Counter	32-bit		
Encoder Mode	Quadrant /CW/ CCW and Pulse/Dir		
Counting Rate	Quadrant Counting: 2 MHz (Max.) CW/CCW: 6 MHz (Max.) Pulse/Dir: 6 MHz (Max.)		
On Voltage Level	+3.5 ~ +5 VDC		
Off Voltage Level	+0.8 VDC Max.		
Programmable digital filter	0.55 ~ 33.3 μs (7 steps)		
Isolation	2500 VDC		




Wire Connections


Digital Input/Digital Output



Analog Input/Analog Output




B Encoder Input



Dimensions (Units: mm)

0

0



Features

1 Data transmission mode

1. Continuous transmission (Maximum sampling rate of 60 kHz per channel) After starting A/D acquisition, data is continuously transmitted to the Host PC.

- 2. After collecting N data samples, the data is transferred to the Host PC (Maximum sampling rate of 128 kHz per channel)
 - (a) After starting A/D acquisition, the data will be temporarily stored in the memory on the PET-7H24M module, and wait until a command is received from the Host PC, before transferring the collected data to the Host PC.
 - (b) The memory capacity allows temporary storage of up to 1500 million data samples.



A/D trigger mode


Software AD Data Acquisition mode

The A/D acquisition parameters are configured via a command from the Host PC. The continuous A/D acquisition or the acquisition of N data samples begins after the command is triggered.

Analog Threshold Trigger


Analog Threshold Trigger is triggered when the voltage signal of the specified analog input channel is higher or lower than a certain voltage setting. In addition, the user can also specify the trigger voltage level range of the input signal. Once the signal leaves the high and low level region or the signal enters the high and low level region, it is triggered to start the acquisition.

- 1. Above High: The signal is triggered above the high level and collects N data.
- 2. Below Low: The signal is triggered below the low level and collects N data.






3. Leave-region: Trigger when the signal leaves the high and low level region, collect N data.




4. Entry-region: Trigger when the signal enters the high and low level region, collect N data.





4 PC Software Support

- 1. Microsoft VC, C#, VB.NET SDK API and Demo for Windows.
- 2. LabVIEW Toolkit and Demo for Windows.
- 3. Library and Demo for Linux.



Ordering Information

PET-7H24M CR Ethernet High Speed Data Acquisition Module with 4 x AI, 2 x AO,3 x DI, 4 x DO, 1 x Encoder Channels (RoHS)